



### Main

Range	Linergy
Product name	Linergy BS
Product or component type	Copper busbar
Busbar description	Flat bar
Quantity per set	Set of 1

### Complementary

Installation direction	Vertical, operating position: lateral Horizontal, operating position: top Horizontal, operating position: bottom
Installation description	Cubicle - width 650 mm Cubicle - width 650 + 150 mm Cubicle duct - width 300 mm Cubicle duct - width 400 mm
[I <sub>e</sub> ] rated operational current	2150 A at 35 °C
[I <sub>cw</sub> ] rated short-time withstand current	60 kA (1 s) for 2 supports (horizontal position) 85 kA (1 s) for 3 supports (horizontal position) 40 kA (1 s) (horizontal position) 85 kA (1 s) for 2 supports (horizontal position) 50 kA (1 s) (horizontal position)
Permissible current	2150 A at 35 °C for IP ≤ IP31 1900 A at 35 °C for IP > IP31
Busbar cross section	100 x 10 mm
Length	2000 mm
Height	150 mm
Product weight	18.7 kg
Type of busbar connection	Without hole
Support thickness	10 mm

### Environment

Standards	IEC 61439-2
-----------	-------------

Product certifications

ASEFA

## Offer Sustainability

Sustainable offer status

Green Premium product

RoHS (date code: YYWW)

Compliant - since 1751 - Schneider Electric declaration of conformity

[Schneider Electric declaration of conformity](#)

REACH

Reference not containing SVHC above the threshold

[Reference not containing SVHC above the threshold](#)

Product environmental profile

Available

[Product Environmental Profile](#)

Product end of life instructions

Need no specific recycling operations

[End of Life Information](#)

## Contractual warranty

Warranty period

18 months