



Main

Range	Linery
Range compatibility	Linery LGYE
Product or component type	Profile busbar
Busbar description	Linery
Quantity per set	Set of 1

Complementary

Installation direction	Horizontal, operating position: top Horizontal, operating position: bottom
Enclosure/Cubicle description	Cubicle - width 650 mm Cubicle - width 650 + 150 mm Cubicle duct - width 300 mm Cubicle duct - width 400 mm
[Ui] rated insulation voltage	1000 V
[Uimp] rated impulse withstand voltage	12 kV (degree of pollution: 3)
[Ie] rated operational current	1000 A
[Icw] rated short-time withstand current	40 kA (1 s) for 2 supports (horizontal position)
Permissible current	1000 A at 35 °C for IP ≤ IP31 850 A at 35 °C for IP > IP31
Length	2000 mm
Height	150 mm
Width	60 mm
Depth	23 mm
Product weight	2.23 kg
Type of busbar connection	Single t-slot
Connection pitch	Free connection position
Thickness	5 mm

Environment

Standards	IEC 61439-2
-----------	-------------

Product certifications	ASEFA
------------------------	-------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1350 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------
