



### Main

Range	Linery
Product name	Linery LGYE
Product or component type	Profile busbar
Busbar description	Linery
Quantity per set	Set of 1

### Complementary

Installation direction	Horizontal, operating position: top Horizontal, operating position: bottom
Installation description	Cubicle - width 650 mm Cubicle - width 650 + 150 mm Cubicle duct - width 300 mm Cubicle duct - width 400 mm
[Ui] rated insulation voltage	1000 V
[Uimp] rated impulse withstand voltage	12 kV (degree of pollution: 3)
[Ie] rated operational current	1250 A
[Icw] rated short-time withstand current	50 kA (1 s) for 2 supports (horizontal position) 60 kA (1 s) for 3 supports (horizontal position)
Permissible current	1250 A at 35 °C for IP ≤ IP31 1050 A at 35 °C for IP > IP31
Length	2000 mm
Height	150 mm
Width	60 mm
Depth	23 mm
Product weight	2.54 kg
Type of busbar connection	Single t-slot
Connection pitch	Free connection position
Support thickness	5 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1350 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------