



Main

Range	Linery
Product name	Linery LGYE
Product or component type	Profile busbar
Busbar description	Linery
Quantity per set	Set of 1

Complementary

Installation direction	Horizontal, operating position: top Horizontal, operating position: bottom
Installation description	Cubicle - width 650 mm Cubicle - width 650 + 150 mm Cubicle duct - width 300 mm Cubicle duct - width 400 mm
[Ui] rated insulation voltage	1000 V
[Uimp] rated impulse withstand voltage	12 kV (degree of pollution: 3)
[Ie] rated operational current	4000 A
[Icw] rated short-time withstand current	60 kA (1 s) for 2 supports (horizontal position) 85 kA (1 s) for 3 supports (horizontal position) 100 kA (1 s) for 4 supports (horizontal position)
Permissible current	3620 A at 35 °C for IP ≤ IP31 3350 A at 35 °C for IP > IP31
Length	2000 mm
Height	200 mm
Width	150 mm
Depth	31 mm
Product weight	22.26 kg
Type of busbar connection	Double t-slot
Connection pitch	Free connection position
Support thickness	10 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1350 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------