



### Main

Range	Linery
Product name	Linery LGY
Product or component type	Connection
Accessory / separate part category	Current distribution accessory

### Complementary

Cubicle-device connection	10 mm horizontal busbar Vertical busbar Linery busbar
Poles description	3P 4P
Installation description	Cubicle - width 400 mm
Installed device	Compact : fixed NS630b...1000 - control: toggle vertical installation Compact : fixed NS1250 - control: toggle vertical installation Compact : fixed NS630b...1000 - control: direct front rotary handle vertical installation Compact : fixed NS1250 - control: direct front rotary handle vertical installation Compact : fixed NS630b...1000 - control: motor mechanism vertical installation Compact : fixed NS1250 - control: motor mechanism vertical installation Compact : fixed NS1600 - control: toggle vertical installation Compact : fixed NS1600 - control: direct front rotary handle vertical installation Compact : fixed NS1600 - control: motor mechanism vertical installation Masterpact : fixed NT06...10 - control: toggle vertical installation Masterpact : fixed NT12 - control: toggle vertical installation Masterpact : drawout NT06...10 - control: toggle vertical installation Masterpact : drawout NT12 - control: toggle vertical installation Masterpact : fixed NT16 - control: toggle vertical installation Masterpact : drawout NT16 - control: toggle vertical installation
[Ie] rated operational current	1600 A
Quantity per set	Set of 1
Product weight	1.52 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0819 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations <a href="#">End of Life Information</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------