



### Main

Range	Prisma
Product name	Prisma PH
IP degree of protection	IP55
Product or component type	Door
Enclosure mounting	Floor-standing
Type of door	Plain
Provided equipment	Handle Keylock (key 405)

### Complementary

Door opening side	Reversible
Installation description	Cubicle - width 700 mm
Number of vertical modules [50 mm]	36
Enclosure material	Treated sheet steel
Quantity per set	Set of 1
Height	2000 mm
Width	700 mm
Colour	White RAL 9001

### Environment

IK degree of protection	IK10 conforming to EN/IEC 62262
Standards	EN/IEC 61439-1

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1751 - Schneider Electric declaration of conformity

Schneider Electric declaration of conformity

REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>