

Product data sheet

Specifications



WALL-MOUNTED ENCLOSURE 3 ROWS PRISMA PACK 160 IP30

08003

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Enclosure/Cubicle Description	Wall-mounted enclosure - width 555 mm
Enclosure Mounting	Flush with kit Surface
Provided Equipment	1 x enclosure 1 x earthing kit 3 x front plate 3 x modular rail
Type Of Front Plate	Modular
Number Of Vertical Modules [50 Mm]	9
Number Of Horizontal Rows	3
Number Of 18 Mm Modules Per Row	24
Standards	IEC 61439-2 IEC 62208 IEC 61439-3 IEC 61439-1

Complementary

[Ui] Rated Insulation Voltage	750 V on main rear busbars conforming to IEC 61439-2
Network Frequency	50/60 Hz
[In] Rated Current	160 A at 40 °C conforming to IEC 61439-2
[Icw] Rated Short-Time Withstand Current	25 kA 1 s conforming to IEC 61439-2
[Ipk] Rated Peak Withstand Current	53 kA conforming to IEC 61439-2
Electrical Insulation Class	Class I
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Smooth Matt
Colour	White (RAL 9001)
Width	555 mm
Height	630 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	157 mm
Net Weight	10.14 kg
Quantity Per Set	Set of 1

Environment

Ip Degree Of Protection	IP30 with door IP31 with door and canopy IP43 with door, canopy and IP43 gasket IP30 without door
Ik Degree Of Protection	IK07 without door conforming to EN/IEC 62262 IK08 with door

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	57.0 cm
Package 1 Length	65.0 cm
Package 1 Weight	11.06 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	10
Package 2 Height	105.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	122.6 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---