



### Main

Range	Prisma
Product name	Pack 160
IP degree of protection	IP30 with door IP30 without door IP31 with door and canopy IP43 with door, canopy and IP43 gasket
Product or component type	Enclosure
Enclosure type	Modular enclosure
Enclosure mounting	Surface Flush with kit
Type of front plate	Modular
Number of vertical modules [50 mm]	18
Number of 18 mm modules per row	24
Provided equipment	Enclosure (x1) Earthing kit (x1) Front plate (x6) Modular rail (x6)

### Complementary

Installation description	Pack enclosure - width 555 mm
[Ui] rated insulation voltage	750 V on main rear busbars conforming to IEC 61439-2
[In] rated current	160 A at 40 °C conforming to IEC 61439-2
[Icw] rated short-time withstand current	25 kA (1 s) conforming to IEC 61439-2
[Ipk] rated peak withstand current	53 kA conforming to IEC 61439-2
Network frequency	50/60 Hz
Number of horizontal rows	6
Enclosure material	Enclosure : treated sheet steel
Quantity per set	Set of 1
Height	1080 mm

Width	555 mm
Depth	157 mm
Product weight	16.06 kg
Surface finish	Matt Smooth
Colour	White RAL 9001

## Environment

IK degree of protection	IK07 without door conforming to EN/IEC 62262 IK08 with door
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Standards	IEC 62208 IEC 61439-2 IEC 61439-1 IEC 61439-3

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1809 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------