



Main

Range	Prisma
Product name	Prisma Pack 250
IP degree of protection	IP40 with door IP30 without door IP41 with door and canopy IP43 with door, canopy and IP43 gasket
Product or component type	Enclosure
Enclosure type	Modular enclosure delivered in kit form
Enclosure mounting	Surface Flush with kit
Type of front plate	Modular Free 6M zone (to be ordered separately)
Number of vertical modules [50 mm]	33
Number of 18 mm modules per row	24
Provided equipment	Earthing kit (x2) Enclosure (floor stand) (x1) Front plate (x9) Modular rail (x9)

Complementary

Installation description	Pack enclosure - width 600 mm
[Ui] rated insulation voltage	1000 V on main rear busbars conforming to IEC 61439-2
[In] rated current	250 A at 40 °C conforming to IEC 61439-2
[Icw] rated short-time withstand current	25 kA (1 s) conforming to IEC 61439-2
[Ipk] rated peak withstand current	53 kA conforming to IEC 61439-2
Network frequency	50/60 Hz
Number of horizontal rows	9
Enclosure material	Enclosure : treated sheet steel
Additional information	Can be combined side by side
Quantity per set	Set of 1

Height	1830 mm
Width	600 mm
Depth	205 mm
Product weight	34.7 kg
Surface finish	Matt Smooth
Colour	White RAL 9001

Environment

IK degree of protection	IK07 without door conforming to EN/IEC 62262 IK08 with door
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Standards	IEC 62208 IEC 61439-2 IEC 61439-1
Mechanical robustness	Seismic tests : 2.5G conforming to IEC 60068-2-57

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

08074 is replaced by:



Cable management ISM71504

Thorsman Glands - cable gland - grey - M25 - diameter 11 to 17

Qty 1

Reason for Substitution: Rebranding | Substitution date: 31 January 2010 | -