



Main

Range	Prisma
Product name	Pack 160
IP degree of protection	IP30
Product or component type	Door
Enclosure mounting	Surface Flush with kit
Type of door	Plain
Provided equipment	Door Handle Keylock (key 405) Other keylock and insert (to be ordered separately) Hinge (x2)

Complementary

Door opening side	Reversible
Number of locks	1
Door opening angle	130 °
Number of 18 mm modules per row	24
Total number of 18 mm modules	120
Installation description	Pack enclosure - width 555 mm
Number of vertical modules [50 mm]	18
Number of horizontal rows	5
Enclosure material	Treated sheet steel
Quantity per set	Set of 1
Height	930 mm
Width	550 mm
Depth	22 mm
Product weight	5.3 kg
Surface finish	Matt Smooth

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	White RAL 9001
--------	----------------

Environment

IK degree of protection	IK08 conforming to EN/IEC 62262
Standards	IEC 61439-2 IEC 61439-1
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0823 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------