



Main

Range	Prisma
Product name	Pack 160
IP degree of protection	IP30
Product or component type	Door
Enclosure mounting	Surface Flush with kit
Type of door	Transparent
Provided equipment	Door Handle Keylock (key 405) Other keylock and insert (to be ordered separately) Hinge (x2)

Complementary

Door opening side	Reversible
Number of locks	1
Door opening angle	130 °
Number of 18 mm modules per row	24
Total number of 18 mm modules	48
Installation description	Pack enclosure - width 555 mm Extension enclosure - width 555 mm
Number of vertical modules [50 mm]	9
Number of horizontal rows	2
Enclosure material	Handle : polyamide Cover frame : treated sheet steel Glass
Quantity per set	Set of 1
Height	480 mm
Width	550 mm
Depth	22 mm
Product weight	3.3 kg

Material	Glass
Surface finish	Matt Smooth
Colour	White RAL 9001

Environment

IK degree of protection	IK08 conforming to EN/IEC 62262
Standards	IEC 61439-2 IEC 61439-1
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1751 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

08092 is replaced by:



Cable management IMT36152

Mureva BOX - gasket - black - M16

Qty 1

Reason for Substitution: Rebranding | Substitution date: 31 October 2009 | -