

Product data sheet

Specifications



PLAIN DOOR W850 33M PRISMA G IP30

08254

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Door
Range Compatibility	Prisma Prisma G enclosure
Provided Equipment	door handle keylock (key 405) other keylock and insert to be ordered separately 3 hinge
Type Of Door	Plain
Ip Degree Of Protection	IP43 with door, canopy and IP43 gasket IP30 without door IP40 with door IP41 with door and canopy

Complementary

Installation Description	Floor-standing enclosure - width 850 mm
Door Opening Side	Reversible
Number Of Locks	3
Door Opening Angle	130 °
Number Of Vertical Modules [50 Mm]	33
Enclosure Material	Treated sheet steel
Quantity Per Set	Set of 1
Height	1650 mm
Width	850 mm
Depth	40 mm
Net Weight	15.7 kg
Surface Finish	Smooth Matt
Colour	White (RAL 9001)

Environment

Ik Degree Of Protection	IK08 conforming to EN/IEC 62262
Standards	IEC 61439-2 IEC 61439-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
----------------------	--

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.500 cm
Package 1 Width	86.500 cm
Package 1 Length	172.000 cm
Package 1 Weight	18.550 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	13
Package 2 Height	99.500 cm
Package 2 Width	200.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	262.150 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile