



Main

Range	Prisma
Product name	Prisma G
IP degree of protection	IP40 with door IP30 without door IP41 with door and canopy IP43 with door, canopy and IP43 gasket
Product or component type	Door
Type of door	Transparent
Provided equipment	Door Handle Keylock (key 405) Other keylock and insert (to be ordered separately) Hinge (x3)

Complementary

Door opening side	Reversible
Number of locks	3
Door opening angle	130 °
Installation description	Floor-standing enclosure - width 850 mm
Number of vertical modules [50 mm]	27
Enclosure material	Treated sheet steel Glass
Quantity per set	Set of 1
Height	1380 mm
Width	850 mm
Depth	40 mm
Product weight	14.5 kg
Surface finish	Matt Smooth
Colour	White RAL 9001

Environment

IK degree of protection	IK08 conforming to EN/IEC 62262
Standards	IEC 61439-2

