



Main

| | |
|------------------------------------|--|
| Range | Prisma |
| Product name | Prisma G |
| IP degree of protection | IP40 with door IP30 without door IP41 with door and canopy IP43 with door, canopy and IP43 gasket |
| Product or component type | Duct |
| Enclosure type | Functional enclosure delivered in kit form |
| Device application | Low voltage electrical distribution |
| Enclosure mounting | Surface |
| Type of front plate | Without (to be ordered separately) |
| Product compatibility | Floor-standing enclosure - width 600 mm |
| Number of vertical modules [50 mm] | 30 |
| Number of 18 mm modules per row | 10 |

Complementary

| | |
|--|--|
| Installation description | Floor-standing duct - width 300 mm |
| [Ui] rated insulation voltage | 1000 V on main rear busbars conforming to IEC 61439-2 |
| [In] rated current | 630 A at 40 °C conforming to IEC 61439-2 |
| [Icw] rated short-time withstand current | 25 kA (1 s) conforming to IEC 61439-2 |
| [Ipk] rated peak withstand current | 53 kA conforming to IEC 61439-2 |
| Network frequency | 50/60 Hz |
| Enclosure material | Enclosure : treated sheet steel |
| Additional information | Can be combined side by side and one on top of another |
| Quantity per set | Set of 1 |
| Height | 1680 mm, with plinth |
| Width | 300 mm |
| Depth | 205 mm |
| Product weight | 13.42 kg |

| | |
|----------------|----------------|
| Surface finish | Matt Smooth |
| Colour | White RAL 9001 |

Environment

| | |
|-------------------------|--|
| IK degree of protection | IK07 without door conforming to EN/IEC 62262 IK08 with door |
| Protective treatment | Electrophoresis treatment and hot-polymerised polyester epoxy powder |
| Standards | IEC 62208 IEC 61439-2 IEC 61439-1 |
| Mechanical robustness | Seismic tests : 2.5G conforming to IEC 60068-2-57 |

Offer Sustainability

| | |
|----------------------------------|--|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available Product Environmental Profile |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|