



### Main

Range	Prisma
Product name	Prisma G
IP degree of protection	IP55
Product or component type	Door
Type of door	Plain
Provided equipment	Door Handle Keylock (key 405) Other keylock and insert (to be ordered separately) Hinge (x2)

### Complementary

Door opening side	Reversible
Number of locks	3
Door opening angle	180 °
Installation description	Wall-mounted enclosure - width 600 mm Extension enclosure - width 600 mm
Number of vertical modules [50 mm]	19
Enclosure material	Treated sheet steel
Quantity per set	Set of 1
Height	1050 mm
Width	600 mm
Depth	26 mm
Product weight	16.2 kg
Surface finish	Matt Smooth
Colour	White RAL 9001

### Environment

IK degree of protection	IK10 conforming to EN/IEC 62262
-------------------------	---------------------------------

Standards	IEC 61439-2 IEC 61439-1
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0930 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------