



### Main

Range	Prisma
Product name	Prisma G
IP degree of protection	IP55
Product or component type	Door
Type of door	Transparent
Provided equipment	Door Handle Keylock (key 405) Other keylock and insert (to be ordered separately) Hinge (x3)

### Complementary

Door opening side	Reversible
Number of locks	3
Door opening angle	180 °
Installation description	Wall-mounted enclosure - width 600 mm Extension enclosure - width 600 mm
Number of vertical modules [50 mm]	27
Enclosure material	Treated sheet steel Glass
Quantity per set	Set of 1
Height	1450 mm
Width	600 mm
Depth	26 mm
Product weight	19.54 kg
Material	Glass
Surface finish	Matt Smooth
Colour	White RAL 9001

### Environment

IK degree of protection	IK10 conforming to EN/IEC 62262
Standards	IEC 61439-2

---

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
----------------------	--

---

### Offer Sustainability

---

RoHS (date code: YYWW)	Compliant - since 0930 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
------------------------	---

---

---

Product environmental profile	Available <a href="#">Product Environmental Profile</a>
-------------------------------	--

---

---

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---