

Product data sheet

Specifications



IP55 PLAIN DOOR W800

08528

⚠ Discontinued on: Jan 31, 2024

⚠ To be end-of-service on: Apr 30, 2025

⚠ Discontinued - Service only

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Door
Range Compatibility	Prisma Prisma P cubicle
Provided Equipment	door handle keylock (key 405) other keylock and insert to be ordered separately barrier 150 mm for the side compartment finishing accessory 4 hinge polyurethane joint
Enclosure Mounting	Floor-standing
Type Of Door	Plain
Ip Degree Of Protection	IP55

Complementary

Installation Description	Cubicle - width 800 mm Cubicle - width 650 + 150 mm
Door Opening Side	Reversible
Number Of Locks	3
Door Opening Angle	120 °
Number Of Vertical Modules [50 Mm]	36
Enclosure Material	Treated sheet steel
Quantity Per Set	Set of 1
Height	2000 mm
Width	800 mm
Depth	30 mm
Net Weight	30.34 kg
Surface Finish	Smooth Matt
Colour	White (RAL 9001)

Environment

Ik Degree Of Protection	IK10 conforming to EN/IEC 62262
-------------------------	---------------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 61439-2
	IEC 61439-1
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	83.500 cm
Package 1 Length	203.500 cm
Package 1 Weight	29.350 kg
Unit Type Of Package 2	P2M
Number Of Units In Package 2	10
Package 2 Height	83.000 cm
Package 2 Width	200.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	303.400 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information