



Main

Range	Prisma
Product name	Prisma P
IP degree of protection	IP55
Product or component type	Door
Enclosure mounting	Floor-standing
Type of door	Transparent
Provided equipment	Door Handle Keylock (key 405) Other keylock and insert (to be ordered separately) Polyurethane joint Hinge (x4)

Complementary

Door opening side	Reversible
Number of locks	3
Door opening angle	120 °
Installation description	Cubicle - width 650 mm
Number of vertical modules [50 mm]	36
Enclosure material	Treated sheet steel Glass
Quantity per set	Set of 1
Height	2000 mm
Width	650 mm
Product weight	24.76 kg
Surface finish	Matt Smooth
Colour	White RAL 9001

Environment

IK degree of protection	IK10 conforming to EN/IEC 62262
Standards	IEC 61439-2 IEC 61439-1

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
----------------------	--

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0813 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------
