



Main

Range	Prisma
Product name	Prisma P
IP degree of protection	IP30
Product or component type	Cover frame
Enclosure mounting	Floor-standing
Type of door	Cover frame
Provided equipment	Cover frame

Complementary

Door opening angle	120 °
Installation description	Cubicle - width 650 mm
Number of vertical modules [50 mm]	36
Quantity per set	Set of 1
Height	2000 mm
Width	650 mm
Product weight	6.76 kg
Material	Steel
Surface finish	Matt Smooth
Colour	White RAL 9001

Environment

IK degree of protection	IK08 conforming to EN/IEC 62262
Standards	IEC 61439-2 IEC 61439-1
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1018 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------