



Main

Range of product	Thorsman
Product or component type	Wall plug
Device short name	TP
Provided equipment	Without screw
Device application	Lightweight installation
Drilling diameter	5.5 mm brick 5.5 mm concrete 5 mm ALC concrete
Drilling depth	≥ 25 mm
Screw diameter	3.5...5 mm
Material	PEHD (polyethylene high density)

Complementary

Practical load capacity	0.4 kN shear solid brick 4.5 0.2 kN pull-out load solid brick 6 0.1 kN shear low density concrete 500 and expanded clay 4.5 0.5 kN shear concrete C25 4.5 0.25 kN pull-out load concrete C25 6 0.04 kN pull-out load low density concrete 500 and expanded clay 6
Practical load capacity	50 kg shear concrete C25 4.5 25 kg pull-out load concrete C25 6 40 kg shear solid brick 4.5 20 kg pull-out load solid brick 6 10 kg shear low density concrete 500 and expanded clay 4.5 4 kg pull-out load low density concrete 500 and expanded clay 6
Colour tint	Yellow
Ambient air temperature for operation	-50...80 °C
Diameter	5.5 mm
Length	22 mm

Environment

Quantity per set	Set of 100
Sale per indivisible quantity	1
Product weight	0.00035 kg

Contractual warranty

Warranty period	18 months
-----------------	-----------
