



Main

Range of product	Thorsman
Product or component type	Wall plug
Device short name	TP
Provided equipment	Without screw
Device application	Lightweight installation
Drilling diameter	6 mm brick 6 mm concrete 6 mm ALC concrete
Drilling depth	≥ 35 mm
Screw diameter	3.5...5 mm
Material	PEHD (polyethylene high density)

Complementary

Practical load capacity	0.6 kN shear concrete C25 4.5 0.4 kN pull-out load concrete C25 6 0.5 kN shear solid brick 4.5 0.3 kN pull-out load solid brick 6 0.2 kN shear low density concrete 500 and expanded clay 4.5 0.08 kN pull-out load low density concrete 500 and expanded clay 6
Practical load capacity	20 kg shear low density concrete 500 and expanded clay 4.5 60 kg shear concrete C25 4.5 8 kg pull-out load low density concrete 500 and expanded clay 6 40 kg pull-out load concrete C25 6 50 kg shear solid brick 4.5 30 kg pull-out load solid brick 6
Colour tint	Red
Ambient air temperature for operation	-50...80 °C
Diameter	6 mm
Length	30 mm

Environment

Quantity per set	Set of 250
Sale per indivisible quantity	1
Product weight	0.00068 kg

Contractual warranty

Warranty period	18 months
-----------------	-----------
