

Product data sheet

Specifications



Thorsman - TP 4 - wall plug - without screw - set of 5000

1007806

Main

Range Of Product	Thorsman
Product Or Component Type	Wall plug
Device Short Name	TP
Device Application	Lightweight installation
Drilling Diameter	12 mm concrete 10 mm ALC concrete
Minimum Drilling Depth	65 mm
Screw Diameter	8...10 mm
Material	PEHD (polyethylene high density)

Complementary

Practical Load Capacity	Shear: 3 kN for concrete C25 4.5) Pull-out load: 2 kN for concrete C25 6) Shear: 0.5 kN for low density concrete 500 and expanded clay 4.5) Pull-out load: 0.25 kN for low density concrete 500 and expanded clay 6)
Practical Load Capacity	Shear: 50 kg for solid brick 4.5) Shear: 300 kg for concrete C25 4.5) Pull-out load: 200 kg for concrete C25 6) Pull-out load: 25 kg for solid brick 6)
Colour Tint	Green
Ambient Air Temperature For Operation	-50...80 °C
Diameter	12 mm
Length	60 mm

Environment

Quantity Per Set	Set of 5000
Sale Per Indivisible Quantity	1
Type Of Packing	Bag
Net Weight	0.0047 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.600 cm
Package 1 Width	1.600 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	6.000 cm
Package 1 Weight	4.200 g
Unit Type Of Package 2	PAL
Number Of Units In Package 2	60000
Package 2 Height	80.000 cm
Package 2 Width	102.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	274536.000 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations