



Main

| | |
|------------------------------------|----------------------|
| Range | Multi 9 |
| Product or component type | Comb busbar |
| Accessory / separate part category | Connection accessory |
| Lines description | 3L |
| Length in 18 mm modules | 12 |

Complementary

| | |
|--|---|
| Number of ways | 4 ways 3 L |
| Poles configuration for 1 way | 1 x 3P |
| Connection pitch | 18 mm |
| Connector type | Tooth |
| Distance between way | 54 mm |
| Insulation | Insulated |
| Device presentation | Uncuttable |
| [Ie] rated operational current | 100 A (40 °C) |
| [Ue] rated operational voltage | 240 V AC 50/60 Hz |
| [Ui] rated insulation voltage | 1000 V AC 50/60 Hz conforming to UL 508 |
| [Uimp] rated impulse withstand voltage | 12 kV conforming to UL 508 |
| Mounting mode | Horizontal |
| Mounting location | Top on tunnel type terminals |
| 9 mm pitches | 24 |
| Width | 216 mm |
| Colour | White (RAL 9001) |
| Range compatibility | Multi 9 C60 / C60 UL489 |

Environment

| | |
|-----------------|--------------------------------------|
| Standards | UL 508 |
| Fire resistance | 960 °C (30 s) conforming to UL 508 |

Offer Sustainability

| | |
|------------------------|---|
| RoHS (date code: YYWW) | Compliant - since 1336 - Schneider Electric declaration of conformity |
|------------------------|---|

 Schneider Electric declaration of conformity

REACH

Reference not containing SVHC above the threshold
Reference not containing SVHC above the threshold

Contractual warranty

Warranty period

18 months
