



Main

Range	Micro Pragma
Product or component type	Enclosure
Enclosure type	Modular enclosure
Nb of 18 mm modules per row	6
Nb of horizontal rows	1
Type of door	Reversible Transparent
Width	140 mm
Height	165 mm
Depth	72 mm

Complementary

Enclosure mounting	Surface
9 mm pitches	12
Total number of 18 mm modules	6
Type of rail	DIN
Enclosure material	Enclosure : self-extinguishing material
Colour	Enclosure : white (RAL 9003)

Environment

Standards	EN 60439-3 IEC 23-48 IEC 60439-3 IEC 60695-2-1
Fire resistance	650 °C (30 s) conforming to IEC 60695-2-1
IP degree of protection	IP30 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102

Contractual warranty

Warranty period	18 months
-----------------	-----------