



### Main

Range	Mini Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Nb of 18 mm modules per row	12
Nb of horizontal rows	1
Provided equipment	Marking kit ( 1 ) Terminal block ( 2 ) Insulating plug ( 1 )
Type of door	Reversible
Width	283 mm
Height	185 mm
Depth	94 mm

### Complementary

Enclosure mounting	Surface
9 mm pitches	24
Total number of 18 mm modules	13
Type of rail	DIN
Number of terminal blocks	2 neutral / earth terminal block with 12 screw connection outgoers
Enclosure material	Enclosure : self-extinguishing material
Colour	Enclosure : white ( RAL 9003 )

### Environment

Standards	IEC 60439-3 IEC 60529 EN 60439-3 IEC 60695-2-1 EN 50102
Product certifications	IMQ
Fire resistance	650 °C ( 30 s ) conforming to IEC 60695-2-1
IP degree of protection	IP30 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---