

Product data sheet

Specifications



Enclosure for modular device,
Mureva Enclosure, 2x12 modules,
without terminal block

10342

Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for modular device
Mounting Plate Description	Without mounting plate

Complementary

Enclosure Mounting	Surface
Number Of 18 Mm Modules Per Row	12
Total Number Of 18 Mm Modules	24
Number Of Horizontal Rows	2
Electrical Insulation Class	Class II Double insulation
Provided Equipment	2 marking kit 2 wiring strap
Type Of Front Cover	Transparent Reversible
Power Dissipation In W	34 W
[In] Rated Current	63 A
Type Of Rail	DIN
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Width	340 mm
Height	460 mm
Depth	160 mm
Internal Depth	88 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)
Targeted Country	Italy

Environment

Standards	IEC 60670 IEC 61439-3 IEC 60695-2-1
-----------	---

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Fire Resistance	650 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.0 cm
Package 1 Width	47.0 cm
Package 1 Length	36.0 cm
Package 1 Weight	3.195 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	23
Package 2 Height	77.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	85.485 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Lower Impact Materials Transparency RoHS/REACH

Resource performance

 Minimum Percentage Of Recycled Plastic Content 27

Well-being performance

 Rohs Exemption Information Yes

 Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations