



Main

Range	Kaedra
Product or component type	Weatherproof enclosure
Enclosure type	Enclosure for plug and socket

Complementary

Enclosure mounting	Surface
Number of 18 mm modules per row	4
Total number of 18 mm modules	4
Number of horizontal rows	1
Electrical insulation class	Class II Double insulation
Number of openings of interface	1
Type of front cover	Transparent
Power dissipation in W	6.5 W
[In] rated current	63 A
Type of rail	DIN
Locking options description	Optional keylock
Enclosure material	Self-extinguishing polymer
Base dimension	65 x 85 mm
Width	98 mm
Height	248 mm
Depth	98.5 mm
Colour	Door : transparent green Enclosure : light grey (RAL 7035)

Environment

Standards	EN 50102 IEC 60439-3
-----------	-------------------------

IEC 60529
IEC 60695-2-1
IEC 670

Fire resistance	650 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Environmental characteristics (UV)	UV resistant class 3 conforming to ISO 4582 2010 Ultraviolet degradation test conforming to ISO 4892-2 2013
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1310 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------