



Main

Range	Domae
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	1L + N
Length in 18 mm modules	57

Complementary

Number of ways	28 ways N + 1 L
Poles configuration for 1 way	1 x 1P + N 1 x 2P
Connection pitch	18 mm
Connector type	Tooth
Distance between way	36 mm
Insulation	Insulated
Device presentation	Cuttable
[Ie] rated operational current	63 A (40 °C)
[Ue] rated operational voltage	400 V AC Ph/Ph 230 V AC Ph/N
[Ui] rated insulation voltage	500 V AC conforming to IEC 61439-1
Mounting mode	Horizontal
Mounting location	Top on tunnel type terminals
9 mm pitches	114
Width	1000 mm
Colour	Light grey (RAL 7035)
Range compatibility	Domae Easy9 MCB Easy9 RCBO Easy9 RCCB Easy9 switch

Environment

Standards	IEC 60664 EN/IEC 60439-1
-----------	-----------------------------

Fire resistance	850 °C (30 s) conforming to IEC 60695-2-1
Pollution degree	3

Contractual warranty

Warranty period	18 months
-----------------	-----------
