



### Main

Range	Domae
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	3L
Length in 18 mm modules	12

### Complementary

Number of ways	4 ways 3 L
Poles configuration for 1 way	1 x 3P
Connection pitch	18 mm
Connector type	Tooth
Distance between way	54 mm
Insulation	Insulated
Device presentation	Cuttable
[Ie] rated operational current	63 A ( 40 °C )
[Ue] rated operational voltage	400 V AC Ph/Ph 230 V AC Ph/N
[Ui] rated insulation voltage	500 V AC conforming to IEC 61439-1
Mounting mode	Horizontal
Mounting location	Top on tunnel type terminals
9 mm pitches	24
Width	220 mm
Colour	Light grey ( RAL 7035 )
Range compatibility	Domae Easy9 MCB Easy9 RCBO Easy9 RCCB Easy9 switch

### Environment

Standards	IEC 60664 EN/IEC 60439-1
Fire resistance	850 °C ( 30 s ) conforming to IEC 60695-2-1

---

Pollution degree	3
------------------	---

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---