

Product data sheet

Specifications



Mini Pragma L surface enclosure - IP30 - 1 x 8 modules - reversible door

10665

⚠ Discontinued on: May 6, 2019

⚠ Discontinued

Main

Range	Mini Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Nb Of 18 Mm Modules Per Row	8
Nb Of Horizontal Rows	1
Provided Equipment	1 marking kit 1 insulating plug
Type Of Door	Reversible
Width	215 mm
Height	168 mm
Depth	94 mm

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	16
Total Number Of 18 Mm Modules	8
Type Of Rail	DIN
Enclosure Material	Enclosure: self-extinguishing material
Colour	Enclosure: white (RAL 9003)

Environment

Standards	EN 60439-3 IEC 60695-2-1 IEC 23-48 IEC 60529 IEC 60439-3 EN 50102
Product Certifications	IMQ
Fire Resistance	650 °C (30 s) conforming to IEC 60695-2-1
Ik Degree Of Protection	IK07 conforming to EN 50102

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	9.5 cm
Package 1 Width	17 cm
Package 1 Length	21.5 cm
Package 1 Weight	0.4 kg

Contractual warranty

Warranty	18 months
----------	-----------