



Main

Range	Mini Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Nb of 18 mm modules per row	12
Nb of horizontal rows	2
Provided equipment	Marking kit (2)
Type of door	Reversible
Width	300 mm
Height	345 mm
Depth	99 mm

Complementary

Enclosure mounting	Flush
9 mm pitches	24
Total number of 18 mm modules	24
Type of rail	DIN
Enclosure material	Enclosure : self-extinguishing material
Colour	Enclosure : white (RAL 9003)

Environment

Standards	IEC 23-48 EN 50102 IEC 60695-2-1 EN 60439-3 IEC 60529 IEC 60439-3
Product certifications	IMQ
Fire resistance	650 °C (30 s) conforming to IEC 60695-2-1
IP degree of protection	IP30 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102

Contractual warranty

Warranty period	18 months
-----------------	-----------
