

Product data sheet

Specifications



Mini Pragma L flush enclosure - IP 30 - 3 x 12 modules - reversible front cover

10678

 **Discontinued on:** May 6, 2019

 **Discontinued**

Main

Range	Mini Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Nb Of 18 Mm Modules Per Row	12
Nb Of Horizontal Rows	3
Provided Equipment	3 marking kit
Type Of Door	Reversible
Width	300 mm
Height	470 mm
Depth	99 mm

Complementary

Enclosure Mounting	Flush
9 Mm Pitches	24
Total Number Of 18 Mm Modules	36
Type Of Rail	DIN
Enclosure Material	Enclosure: self-extinguishing material
Colour	Enclosure: white (RAL 9003)

Environment

Standards	EN 60439-3 IEC 60439-3 EN 50102 IEC 60695-2-1 IEC 23-48 IEC 60529
Product Certifications	IMQ
Fire Resistance	650 °C (30 s) conforming to IEC 60695-2-1
Ik Degree Of Protection	IK07 conforming to EN 50102

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	9.5 cm
Package 1 Width	30 cm
Package 1 Length	47 cm
Package 1 Weight	1.305 kg

Contractual warranty

Warranty	18 months
----------	-----------