

Product data sheet

Specifications



Defem - pendant - B12L - steel, hot-dip galvanized - light installation

1149236

⚠ Discontinued on: Mar 14, 2018

⚠ End-of-service on: Apr 23, 2018

⚠ Discontinued

Main

Range	Defem
Product Or Component Type	Pendant
Device Short Name	B12L
Device Application	Light installation

Complementary

Material With Surface Treatment	Steel (hot-dip galvanized)
Atmospheric-Corrosivity Category	C3/C4
Fixing Mode	By bolt M8/M10
Product Compatibility	Extension B19
Height	250 mm
Width	145 mm
Depth	60 mm
Net Weight	69 kg / set of 100

Environment

Environmental Characteristic	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants
------------------------------	---

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6 cm
Package 1 Width	14.5 cm
Package 1 Length	25 cm
Package 1 Weight	690 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations