


Product data sheet

Specifications



Thorsman - TPS-4/5x25 - nail plug - with screw - set of 100

1149301

 **Discontinued on:** Dec 12, 2016

 **Discontinued**

Main

Range Of Product	Thorsman
Product Or Component Type	Nail plug
Device Short Name	TPS
Provided Equipment	Screw
Drilling Diameter	4 mm
Minimum Drilling Depth	30 mm
Screw Diameter	2.5 mm

Complementary

Colour Tint	Clear
Material	Nail plug: PA (polyamide) Screw: steel electroplated
Practical Load Capacity	Shear: 0.15 kN for concrete C25 4.5) Pull-out load: 0.05 kN for concrete C25 6) Shear: 0.15 kN for solid brick 4.5) Pull-out load: 0.05 kN for solid brick 6)
Thickness	0...5 mm fixture
Ambient Air Temperature For Operation	-40...80 °C
Diameter	7 mm
Length	45 mm

Environment

Quantity Per Set	Set of 100
Net Weight	0.0015 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.7 cm
Package 1 Width	0.7 cm
Package 1 Length	4.4 cm
Package 1 Weight	1.5 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------