



Main

| | |
|---------------------------|--------------|
| Range of product | Thorsman |
| Product or component type | Nail plug |
| Device short name | TPS |
| Provided equipment | Screw |
| Drilling diameter | 4 mm |
| Drilling depth | ≥ 40 mm |
| Screw diameter | 2.5 mm |

Complementary

| | |
|---------------------------------------|--|
| Colour tint | Clear |
| Material | PA (polyamide) nail plug Steel electroplated screw |
| Practical load capacity | 0.15 kN shear concrete C25 4.5 0.05 kN pull-out load concrete C25 6 0.15 kN shear solid brick 4.5 0.05 kN pull-out load solid brick 6 |
| Thickness | 0...15 mm fixture |
| Ambient air temperature for operation | -40...80 °C |
| Diameter | 7 mm |
| Length | 55 mm |

Environment

| | |
|------------------|------------|
| Quantity per set | Set of 100 |
| Product weight | 0.0021 kg |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications