

# Product data sheet

Specifications



## Thorsman - TPP-10xM4 - cavity fixing - with screw - set of 25

1200005

### Main

Range Of Product	Thorsman
Product Or Component Type	Cavity fixing
Device Short Name	TPP
Provided Equipment	Screw
Mounting Support	Board material - thickness: 10...30 mm
Device Application	10...26 mm board material
Mounting Support	Ceiling Wall mounted
Thread Type	M4
Screw Diameter	4 mm
Screw Length	55 mm
Drilling Diameter	10 mm
Colour Tint	Metal Grey

### Complementary

Quantity Per Set	Set of 25
Net Weight	0.0105 kg

### Environment

Material	Screw: steel electroplated Toggle: zinc Collar: zinc Spring: steel
Practical Load Capacity	Shear: 400 N for 13 mm board 2.5) Pull-out load: 160 N for 13 mm board 3) Shear: 600 N for 2 x 13 mm board 2.5) Pull-out load: 220 N for 2 x 13 mm board 3)
Thickness	0...37 mm fixture 13 mm board 0...24 mm fixture 2 x 13 mm board
Ambient Air Temperature For Operation	-20...80 °C

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	3.500 cm
Package 1 Length	6.000 cm
Package 1 Weight	10.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	25
Package 2 Height	4.600 cm
Package 2 Width	7.000 cm
Package 2 Length	10.400 cm
Package 2 Weight	268.000 g
Unit Type Of Package 3	P12
Number Of Units In Package 3	35200
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	388.640 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations