



### Main

Range	Kaedra
Product or component type	Weatherproof enclosure
Enclosure type	Enclosure for plug and socket
Accessories included with enclosure	1 terminal block 4 holes

### Complementary

Enclosure mounting	Surface
Number of 18 mm modules per row	4
Total number of 18 mm modules	4
Number of horizontal rows	1
Electrical insulation class	Class II Double insulation
Number of openings of interface	1
Provided equipment	1 terminal block 4 holes
Type of front cover	Transparent
Power dissipation in W	6.5 W
[In] rated current	63 A
Number of pre-cutouts PG ISO	1
Number of terminal blocks	1 with 4 outgoers
Distribution block outgoers	2 x 10 mm <sup>2</sup> 2 x 16 mm <sup>2</sup>
Locking options description	Optional keylock
Enclosure material	Self-extinguishing polymer
Base dimension	65 x 85 mm
Width	98 mm
Height	248 mm
Depth	98.5 mm
Colour	Door: transparent green

## Environment

Standards	IEC 670 EN 50102 IEC 60439-3 IEC 60529 EN 50262
Fire resistance	750 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Environmental characteristics (UV)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations <a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------