

Product data sheet

Specifications



Kaedra - for plug and socket - 6 openings - 1 x 12 modules - 1 terminal block

13156

⚠ Discontinued on: Dec 31, 2023

⚠ Discontinued

Main

Range	Kaedra
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for plug and socket
Accessories Included With Enclosure	6 plates for 65 x 85 power outlets 1 terminal block 8 holes 1 terminal block support 2 wiring straps 2 plates for push-button controls
Mounting Plate Description	Without mounting plate

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	24
Number Of 18 Mm Modules Per Row	12
Total Number Of 18 Mm Modules	12
Number Of Horizontal Rows	1
Electrical Insulation Class	Double insulation Class II
Number Of Openings Of Interface	6
Number Of Plates	2 for push-button controls 6 for 65 x 85 power outlets
Provided Equipment	2 wiring strap 6 plate for 65 x 85 power outlet 1 terminal block 8 holes 1 terminal block support 2 plate for push-button control
Type Of Front Cover	Transparent
Power Dissipation In W	23 W
[In] Rated Current	63 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	17
Number Of Terminal Blocks	1 with 8 outgoers
Distribution Block Outgoers	4 x 10 mm ² 4 x 16 mm ²
Locking Options Description	Optional keylock

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Enclosure Material	Self-extinguishing polymer
Base Dimension	90 x 100 mm
Width	340 mm
Height	460 mm
Depth	160 mm
Internal Depth	91 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

Environment

Standards	IEC 60439-3 IEC 60529 EN 50102 EN 50262 IEC 670
Fire Resistance	750 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	47.000 cm
Package 1 Width	36.000 cm
Package 1 Length	16.800 cm
Package 1 Weight	2.850 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	28
Package 2 Height	113.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	95.384 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Circularity Profile	No need of specific recycling operations