



Main

Range	Kaedra
Product or component type	Weatherproof enclosure
Enclosure type	Versatile enclosure for power outlet

Complementary

Enclosure mounting	Surface
Number of 18 mm modules per row	5
Total number of 18 mm modules	5
Number of horizontal rows	1
Electrical insulation class	Class II Double insulation
Type of front cover	Transparent
Power dissipation in W	12 W
[In] rated current	63 A
Type of rail	DIN
Number of pre-cutouts PG ISO	3
Locking options description	Optional keylock
Enclosure material	Self-extinguishing polymer
Width	138 mm
Height	460 mm
Depth	160 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

Environment

Standards	IEC 60529 EN 50102 IEC 670 IEC 60439-3
-----------	---

EN 50262

Fire resistance	750 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Environmental characteristics (UV)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------