

Product data sheet

Characteristics

15208

modular frequency meter 20 to 100 Hz iFRE - 230V



Main

Range	Acti 9
Device short name	IFRE
Product or component type	Frequency meter
Range compatibility	Prisma G door Prisma P door
Type of measurement	Frequency
Display type	LED : 3 digit(s)
Maximum value measured	99.9 Hz

Complementary

Frequency measurement range	20...100 Hz
Full scale display	99,9
Measurement accuracy	0.5 % +/- 1 digit
[Us] rated supply voltage	230 V AC 50/60 Hz
Power consumption in VA	< 5 VA
Mounting mode	Fixed
Mounting support	DIN rail

Environment

Standards	EN 65081-1 EN 65081-2 IEC 65081-1 IEC 65081-2
IP degree of protection	IP20 terminal level IP40 front face
Width	36 mm
Height	87 mm
Depth	65 mm

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0608 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------
