



Main

Range	Acti 9
Device short name	IAMP
Product or component type	Ammeter
Range compatibility	Prisma G door Prisma P door
Mounting support	DIN rail

Complementary

Type of measurement	Current
[Us] rated supply voltage	230 AC 50/60 Hz
Power consumption in VA	0.3 VA
Power consumption in VA	0.3 VA
9 mm pitches	4
Width	36 mm
Height	87 mm
Depth	65 mm
Connections - terminals	Tunnel type terminal 2 cable(s) 2.5 mm ²

Environment

Standards	EN 50081-1 EN 50082-1 IEC 61010-1
Ambient air temperature for operation	-20...50 °C

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0548 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
