

Product data sheet

Specifications



modular bell transformer - 230 V
50..60 Hz - output 8..12 V - 4 VA

15213

⚠ Discontinued on: May 27, 2019

⚠ Discontinued

Main

Product Or Component Type	Transformer
Device Short Name	TR
Transformer Type	Bell transformer

Complementary

[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Output Voltage	8/12 V: +/- 15 % on load 12/16 V: off load
Output Short-Circuit Protection	Built-in
Rated Power In Va	4 VA
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	4
Height	89 mm
Width	36 mm
Depth	60 mm
Auxiliary Connection Terminal	Tunnel type terminals 4 mm²

Environment

Standards	EN 61558-2-6 IEC 61558-2-6 EN 60742
Product Certifications	NF
Overvoltage Category	Class II with terminal shields in option
Ambient Air Temperature For Operation	-20...55 °C
Ambient Air Temperature For Storage	-25...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	4 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	8 cm
Package 1 Weight	0.24 kg

Contractual warranty

Warranty	18 months
----------	-----------