

Product data sheet

Specifications



modular buzzer - 230 V 50/60Hz - 70 dB

15322

⚠ Discontinued on: Apr 1, 2019

⚠ Discontinued

Main

Product Or Component Type	Buzzer
Device Short Name	RO

Complementary

[Us] Rated Supply Voltage	230 V AC at 50/60 Hz
Power Consumption In Va	5 VA
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	2
Height	81 mm
Width	18 mm
Depth	72 mm
Auxiliary Connection Terminal	Tunnel type terminals 4 mm²

Environment

Noise Level	70 dB
Type Of Sound	Buzzer

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.4 cm
Package 1 Width	1.8 cm
Package 1 Length	6.6 cm
Package 1 Weight	0.056 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications