



Main

Product or component type	Buzzer
Device short name	RO

Complementary

[Us] rated supply voltage	230 V AC 50/60 Hz
Power consumption in VA	5 VA
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	2
Height	81 mm
Width	18 mm
Depth	72 mm
Auxiliary connection terminal	Tunnel type terminals 4 mm ²

Environment

Noise level	70 dB
Type of sound	Buzzer

Contractual warranty

Warranty period	18 months
-----------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications