



### Main

Range of product	Acti 9
Product name	Acti 9 IH
Device short name	IH
Product or component type	Mechanical time switch
Number of channels	1
Function available	Manual time changeover

### Complementary

Device application	Building
Load type	10 parallel-corrected fluorescent tube, balast : conventional, ( 58 W ) 15 parallel-corrected fluorescent tube, balast : conventional, ( 40 W ) 230 V AC halogen lamp, ( 1000 W ) 230 V AC incandescent lamp, ( 1000 W ) 3 parallel-corrected fluorescent tube, balast : conventional, ( 100 W ) 7 fluocompact lamp, ( 11 W ) 7 fluocompact lamp, ( 15 W ) 7 fluocompact lamp, ( 20 W ) 7 fluocompact lamp, ( 7 W )
Cycle duration	24 h
Measurement accuracy	+/- 1 s/day
Maximum number of switchings	48 on - 48 off
Minimum interval duration	15 min
Type of setting	Manual time changeover
Measurement accuracy	+/- 1 s/day 20 °C
Power consumption in VA	2.5 VA
Maximum switching current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] rated operational voltage	( +/- 10 % ) 230 V AC 50/60 Hz
Battery life	10 yr
Backup time	100 h time and program saving

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting support	DIN rail
9 mm pitches	2
Colour tint	White (RAL 9003)
Connections - terminals	Screw terminals
IP degree of protection	IP20 B
Width	18 mm
Height	90 mm
Depth	66 mm
Product weight	0.101 kg

## Environment

Ambient air temperature for operation	-10...50 °C
IP degree of protection	Terminals : IP20 B

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0625 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available

## Contractual warranty

Warranty period	18 months
-----------------	-----------