



Main

Range of product	Acti 9
Product name	Acti 9 MIN
Device short name	MIN
Product or component type	Electromechanical timer
Colour tint	White (RAL 9003)

Complementary

Device application	Building
Load type	230 V AC halogen lamp (2300 W) 230 V AC incandescent lamp (2300 W) 5 fluorescent lamp electronic ballast (15 W) 5 fluorescent lamp electronic ballast (20 W) 6 fluorescent lamp electronic ballast (11 W) 9 fluorescent lamp electronic ballast (7 W) dual mounted fluorescent tube conventional ballast (2300 VA) fluocompact lamp conventional ballast (2000 VA) fluorescent tube electronic ballast (300 VA) non-corrected fluorescent tube conventional ballast (2300 VA) parallel-corrected fluorescent tube conventional ballast (1300 VA) serial-corrected fluorescent tube conventional ballast (2300 VA)
Maximum power consumption in VA	1 VA
Maximum switching current	16 A - 230 V AC pf = 1
[Ue] rated operational voltage	230 V AC - 10...15 % at 50 Hz
Time delay	Adjustable from 1 to 7 minutes
Mounting support	DIN rail
9 mm pitches	2
Connections - terminals	Screw terminals - <= 6 mm ²
Width	18 mm
Height	83 mm
Depth	68 mm
Net weight	84 g

Environment

Ambient air temperature for operation	-10...50 °C
IP degree of protection	IP20 B

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------