



Main

Device short name	ATLs
Product or component type	Remote indication auxiliary
Signal contacts composition	1 C/O
Signalling circuit voltage	24 V DC : 0.01...6 A 48 V DC : 0.01...2 A 130 V DC : 0.01...1 A 24...240 V AC : 50/60 Hz 0.01...6 A

Complementary

Mounting mode	Fixed, on right side of TL
Mounting support	DIN rail
9 mm pitches	1
Height	81 mm
Width	9 mm
Depth	60 mm
Colour	Grey
Connections - terminals	Signalling circuit : tunnel type terminals for 2 flexible cable(s) 2.5 mm ² Signalling circuit : tunnel type terminals for 2 rigid cable(s) 1.5 mm ²

Environment

Tropicalisation	2
Relative humidity	95 % (55 °C)
Ambient air temperature for operation	-20...50 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------

15405 is replaced by:



electrical auxiliaries A9C15405

Acti 9 remote indication iATLs

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2011
