



### Main

Product or component type	Impulse relay
Device short name	TL
Device application	Remote control
Poles	1P
Pole contact composition	1 NO
[In] rated current	16 A
Network type	AC
[Uc] control circuit voltage	230 V AC 50 Hz

### Complementary

Network frequency	50 Hz
[Ue] rated operational voltage	250 V AC 50 Hz
Control type	Remote and manual control
Control signal type	Impulse
Switching frequency	5 switching operations/minute
Impulse duration	50 ms
Remote control type	Illuminated push-button 3 mA
Local signalling	ON/OFF indication
Mounting mode	Fixed
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Upside : ProDis
9 mm pitches	2
Height	84 mm
Width	18 mm
Depth	60 mm
Electrical durability	AC-22 : 200000 cycles
Product compatibility	No auxiliary

### Environment

Standards	IEC 60669-1
-----------	-------------

Quality labels	NF
Noise level	60 dB
IP degree of protection	IP2 IP4
Pollution degree	3
Tropicalisation	2
Relative humidity	95 % ( 55 °C )
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...80 °C

### Contractual warranty

Warranty period	18 months
-----------------	-----------