



Main

Range of product	Multi 9
Product name	Multi 9 ERL
Product or component type	Extension for changeover relay
Device short name	ERL
Device application	Extension for changeover relay
Signal contacts composition	1 C/O + 1 NO
[Uc] control circuit voltage	48 V AC 50/60 Hz

Complementary

[Ie] rated operational current	10 A at 230 V AC (cos Phi = 1)
[Ui] rated insulation voltage	250 V AC
Supply holding power	8 VA
Supply inrush power	8 VA
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	2
Electrical durability	AC-21 : 100000 cycles
Connections - terminals	Connection by clip Tunnel type terminals 0.5...6 mm ²

Environment

Standards	IEC 255 NF C 45-250
-----------	------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------