

Product data sheet

Specifications



Changeover relay extension ERL 10A 2P Uc 24VAC Ue 250VAC

15541

 **Discontinued on:** May 2, 2019

 **Discontinued**

Main

Range Of Product	Multi9
Product Name	Multi9 ERL
Product Or Component Type	Extension for changeover relay
Device Short Name	ERL
Device Application	Extension for changeover relay
Signal Contacts Composition	1 C/O + 1 NO
[Uc] Control Circuit Voltage	24 V AC 50/60 Hz

Complementary

[Ie] Rated Operational Current	10 A at 230 V AC (cos Phi = 1)
[Ui] Rated Insulation Voltage	250 V AC
Supply Holding Power	8 VA
Supply Inrush Power	8 VA
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	2
Electrical Durability	AC-21: 100000 cycles
Connections - Terminals	Tunnel type terminals 0.5...6 mm ² Connection by clip

Environment

Standards	NF C 45-250 IEC 255
-----------	------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	1.8 cm
Package 1 Length	7.3 cm
Package 1 Weight	0.117 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------